

# DF 545



by **Shurtape®**

## PROFESSIONAL GRADE, PREMIUM DOUBLE-COATED CLOTH TAPE

### TYPICAL APPLICATIONS

- For securing carpet and pad at convention centers, arenas and hotels
- Can also be used for general purpose hanging applications in the construction and abatement industries
- Also used for splicing applications

### PRODUCT FEATURES

- Excellent adhesion to smooth and irregular surfaces
- High tensile strength
- Easy to unwind
- 30-day indoor, residue-free removal on most surfaces

### CONSTRUCTION

Overall Grade/Function: Professional

Backing: Polyester/cotton blend cloth

Adhesive: Rubber-based

Liner: Siliconized, polyethylene release liner

### STANDARD WIDTH(S)

48 mm

### STANDARD LENGTH(S)

33 m

Contact your Shurtape sales representative for other available sizes

### STANDARD CORE SIZE

3 in

### APPLICABLE STANDARDS

Meets Consumer Product Safety Commission requirements through conformance with ASTM D-4236

### STORAGE AND USAGE CONDITIONS

Tape should be stored in its original packaging in a cool, dry area away from direct sunlight and should be used within 12 months of date of shipment. Surfaces to which tape is applied should be clean, dry and free of grease, oil or other contaminants.

### COLOR(S)



**NATURAL**  
(NAT)

### PHYSICAL PROPERTIES

Tensile Strength

24 lbs/in width

42.0 N/10 mm

Adhesion to Stainless Steel

Exposed Side

52 oz/in width

5.8 N/10 mm

Adhesion to Stainless Steel

Liner Side

64 oz/in width

7.1 N/10 mm

Thickness (Without Liner)

10.5 mils

0.27 mm

Elongation

8%

8%

Service Temperature Range

50 F to 200 F

10 C to 93 C

Physical and performance characteristics shown above are obtained from tests recommended by PTSC, ASTM, government agencies or Shurtape Technologies, LLC, Quality Assurance and Technical Service departments and do not represent product specifications or a guarantee of product performance. Individual rolls may vary from these standards (or physical properties). The user should determine whether the product is fit for a particular purpose and is suitable for the user's method of application before use.

To remove the blue liner, use scissors, a knife or blade to cut a small slit in the tape at the desired length. Then, hand tear the rest of the tape for easy liner separation.

